

7.0 mm x 5.0 mm XO

C85G series

Description:

The C85G Crystal Oscillator (XO) Series products provide a wide range of options in temperature stability, operating temperature range, and frequencies up to 700 MHz in a 7.0 x 5.0 mm ceramic package.



Features:

- Available in frequencies from 325 MHz to 700 MHz.
- Tri-state Enable/Disable
- Hermetically sealed ceramic SMD package
- PECL and LVDS outputs
- RoHS-6/Leadfree compliant

Frequency Range, Operating Temperature, and Frequency Stability:

Frequency	Operating Temperature	Product Code	Freq. Stability	Product Code
325 to 700MHz	-10 to +60C	A	+/- 25 ppm	A
	0 to +70C	B	+/- 50 ppm	B
	-20 to 70C	C	+/- 75 ppm	C
	-40 to 85C	D	+/-100ppm	D

***Frequency stability includes 25C tolerance, drift over temperature, change versus voltage and load, 20 year aging, shock and vibration

Aging: (typical at 622.08MHz after 30 days continuous operation)

Frequency	Timeframe	Aging	Product Code
622.08 MHz	1st Year	+/- 5.0ppm	N/A

Supply Voltage (Vs):

Power Supply (Vs)	3.3 Vdc +/-10%
Product Code	N/A

Supply Voltage Sensitivity (+/- 10%): +/- 2 ppm max. frequency change

Current Consumption (I_{DD}):

Frequency Range (MHz)	I _{DD} (at 3.3V)
325.000 to 700.000	PECL / LVDS
	100 / 80 mA

Environmental:

Storage Temperature	-55 to +125 °C
---------------------	----------------

Output Waveform:

	PECL	LVDS
Product Code	A	B
	At 3.3 V	At 3.3 V
Output Logic 1	2.275Vmin	1.6Vmax
Output Logic 0	1.680Vmax	0.9Vmin
Rise/Fall Time (nS)	1 max	1 max


Start-up Time: 3 mS max.

Tri-state function Pin 2:

Pin 2 = Output Active with 2.0 V or 2.5 V with 3.3V supply


Ordering Options:

Product Family	Operating Temperature	Frequency Stability	Output Type	Operating Frequency
C85G	A	A	A	XXX.XXXMHz
C85G	B	B	B	XXX.XXXMHz
C85G	C	C		XXX.XXXMHz
C85G	D	D		XXX.XXXMHz



****Consult Bliley sales if other options required**

RoHs compliant; -20 to 70C; +/- 25 ppm; PECL outputs and 325 MHz nominal operating frequency



PE200-1

How to Order This Product:

Contact Bliley Technologies with Product Selection Code from Ordering Options Section above.

Attn:

Sales @ Bliley

Fax: **814-833-2712**

Phone: 814-838-3571

Email: info@bliley.com

Web: www.bliley.com

Date: _____

From:

Name: _____ Company: _____

Fax: _____ Phone: _____

Email: _____

Quantities to Quote: _____ Target Price: \$_____

Application / Reference #: _____